



Graver Technologies

Filtration | Separation | Purification

RTEC™ Series Resin Bonded Filter Cartridges

Rigid Resin Bonded Filters

RTEC Series filters feature an acrylic fiber/phenolic resin construction that produces an extremely rigid pore structure. This construction allows the filter to withstand extremes of viscosity and temperature without compression or collapse. In addition, a true graded density construction allows complete utilization of the filter's depth, with coarse particles captured in the outer zones and finer particles captured nearer the core.

RTEC Series Features - Benefits

- Rigid acrylic fiber/phenolic resin construction prevents unloading even at high differential pressures
- Grooved outer surface increases surface area for longer on-stream life
- Available in a wide range of removal efficiencies from 1 to 100 microns
- Available with optional end configurations for installation in most housings
- No metal or plastic cores for easier disposal
- Broad chemical compatibility



Filter Specifications

Media:	Acrylic Fiber/Phenolic Resin
Optional End Caps:	Polyester
Multi length bonding agent:	Polyamide Hot Melt
Gasket/O-Rings:	Silicone, EPDM, Buna N, Viton and Teflon encapsulated Viton (o-rings only)
Micron ratings:	1, 3, 5, 10, 25, 50, 75, 100

Dimensions

Nominal lengths:	9.75, 10, 19.5, 20, 29.25, 30, 39, 40 inches (24.8, 25.4, 49.5, 50.8, 74.3, 76.2, 99.1, 101.6 cm)
Outside diameter:	2.45 in (6.22 cm)
Inside diameter:	15/16 in (2.38 cm)

Operating Conditions

Maximum operating temperature:	252°F (122°C) for 9.75" length in liquids 212°F (100°C) for lengths other than 9.75" in liquids 176°F (80°C) in gas
Maximum differential pressure:	70 psid (4.8 bar)
Recommended changeout differential pressure:	35psid (2.4 bar)

Applications

- Paints, Inks
- Sealants
- Adhesives
- Lacquers, Varnishes, Shellacs
- Fuel Oils, Crude Oils, Grease
- Machine Coolants
- Silicones
- Antifreeze
- Plasticizers
- Animal Oils

RTEC Series Nomenclature Information

RTEC	5	-20	N	N
Product Series	Retention Rating (microns)	Length (inches)	End Configuration	Gasket or O-Ring
RTEC	1	9.75	P Double Open End	S Silicone
Resin Bonded	3	10	P2 226/Flat Single Open End	B Buna-N
Filter Series	5	19.5	P3 222/Flat Single Open End	E EPDM
	10	20	P7 226/Fin Single Open End	V Viton
	25	29.25	P8 222/Fin Single Open End	T Teflon encap. Viton (O-rings only)
	50	30	N None	N None
	75	39		
	100	40		

Example: RTEC 5-20 NN

Flow Rate Nomograph

To determine the flow rate and pressure drop for a specific application, first determine your required flow rate per single length cartridge, then refer to the nomograph on the right and proceed as follows:

1. Select the required micron grade from the "RATING" line.
2. Using a straightedge, draw a line from the grade mark, through the desired "DIFFERENTIAL PRESSURE", to the "INDEX" line.
3. Choose the viscosity of the fluid to be filtered on the "VISCOSITY" line.
4. Using a straightedge, draw a line from the viscosity mark, intersecting the mark made previously on the "INDEX" line, to the "FLOW RATE" line. Ensure the resulting flow rate does not exceed that set out in the table on the nomograph.
5. Repeat the exercise at various differential pressures, to achieve an acceptable combination of flow rate and differential pressure to meet your specific requirement.

Note:

For chemical compatibility, flow rates, and temperature requirements please consult the factory or your local Graver distributor.

For more information

Graver Technologies Customer Service: **1-888-353-0303**


Technical Support: **1-800-510-0932**

E-mail us at info@gravertech.com

Graver Technologies Europe (UK): **+44-1424-777791**

All information and recommendations appearing in this bulletin concerning the use of products described herein are based on tests believed to be reliable. However, it is the user's responsibility to determine the suitability for his own use of such products. Since the actual use by others is beyond our control, no guarantee, expressed or implied, is made by Graver Technologies as to the effects of such use or the results to be obtained. Graver Technologies assumes no liability arising out of the use by others of such products. Nor is the information herein to be construed as absolutely complete, since additional information may be necessary or desirable when particular or exceptional conditions or circumstances exist or because of applicable laws or government regulations.

RTEC is a trademark of Graver Technologies, LLC.



DISTRIBUTED BY:



Graver Technologies

200 Lake Drive
Glasgow,
DE 19702 U.S.A.

302-731-1700
800-249-1990
Fax: 302-369-0938

e-mail: info@gravertech.com
web site: www.gravertech.com

